

NOTES:

1. SUBSTRATE: N-SF6
2. COATING
S1: NONE
S2: NONE

△ 3. EDGES: FINE GRIND SURFACE



4. CENTERING: < 3 ARCMIN

5. ASPHERIC FIGURE ERROR: 0.016 μm RMS

△ 6. ASPHERIC SURFACE DESCRIBED BY THE FOLLOWING EQUATION AND COEFFICIENTS SHOWN IN TABLE BELOW

$$Z(Y) = \frac{\left(\frac{1}{\text{RADIUS}}\right) * Y^2}{1 + \sqrt{1 - (1+k) * \left(\frac{1}{\text{RADIUS}}\right)^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14} + M * Y^{16}$$

7. ROHS: COMPLIANT



COEFFICIENT TABLE △ 6.

	S1
SEMI-DIAMETER	2.500000E+01
COEFFICIENT	
(1/RADIUS)	2.483917E-02
k	-7.704650E-01
D	0.000000E+00
E	1.478988E-07
F	-7.467807E-11
G	-5.681265E-17
H	1.944793E-15
J	0.000000E+00
L	0.000000E+00
M	0.000000E+00

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
RADIUS	40.26	INFINITY
SURFACE QUALITY	40 - 20	40 - 20
CLEAR APERTURE	Ø45.00	Ø45.00
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL: 50.00mm

BFL: 42.77mm

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm



Edmund Optics®

TITLE

50mm Dia x 50mm FL, Uncoated,
High Precision Aspheric Lens

DWG NO

12448

SHEET
1 OF 1