



NOTES:

- 1. COATING (APPLY ACROSS COATING APERTURE)
Laser V-Coat (532nm)
R(ABS) <0.25% @ 532nm
- 2. RoHS: COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD (PULSED)	10 J/cm ² @ 532nm, 20ns, 20Hz
DESIGN WAVELENGTH DWL (nm)	532
EXPANSION POWER	1.5X
TRANSMISSION (%)	>99 (nominal)
NOMINAL PERFORMANCE	< $\lambda/10$ for 4mm input beam (nominal, λ = DWL)

THIRD ANGLE
PROJECTION

ALL DIMS IN mm

 Edmund Optics®			
TITLE	1.5X, 532nm Vega™ Nd:YAG Laser Line Beam Expander		
DWG NO	12874	SHEET 1 OF 1	