





FOCAL LENGTH (EFL): 75 ± 0,75
BACK FOCAL LENGTH (BFL): 72,31

- 1 266nm Laser AR Coating
R(ABS) < 0,25% @ 266nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE					
R 35,707 CX			GLASS Fused Silica 458/678	R ∞ PL					
Øe 11,7				Øe 11,7					
⌈ SEE NOTE 1				⌈ SEE NOTE 1					
3/ 2 (0,2) λ=632,8 nm				3/ 2 (0,2) λ=632,8 nm					
4/ -				4/ 2,18'					
5/ 10 - 5				5/ 10 - 5					
6/ 3J-cm ⁻² ; 266nm; 20ns [20Hz]				6/ 3J-cm ⁻² ; 266nm; 20ns [20Hz]					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	λ = 355nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY						TITLE	12,7mm Dia x 75mm FL, 266nm Laser AR Coating, 3J Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	38661	SHEET SIZE	A4	SHEET 1 OF 1