



NOTES:

1. SUBSTRATE: POLYMER FILM XP40HT-40
2. WAVELENGTH RANGE: 400 - 700 nm
3. POLARIZATION EFFICIENCY (%): > 99.99
4. TRANSMISSION (%):  
SINGLE:  $40 \pm 2$   
PARALLEL: 32.2  
CROSSED: <0.007
5. EXTINCTION RATIO: 5000:1
6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

|                           |    |        |                                                                    |                 |
|---------------------------|----|--------|--------------------------------------------------------------------|-----------------|
| THIRD ANGLE<br>PROJECTION |    | TITLE  | 300 x 300mm HIGH-TEMPERATURE LINEAR<br>POLARIZING FILM (XP40HT-40) |                 |
| ALL DIMS IN               | mm | DWG NO | 14350                                                              | SHEET<br>1 OF 1 |