





FOCAL LENGTH (EFL): 300 ± 3

BACK FOCAL LENGTH (BFL): 297,38

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 142,827 CX Øe 11,7 λ - 3/ 2 (0,2) $\lambda=632,8$ nm 4/ - 5/ 10 - 5 6/ -		GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 λ - 3/ 2 (0,2) $\lambda=632,8$ nm 4/ 2,18' 5/ 10 - 5 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE $\lambda = 355\text{nm}$ SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 12,7mm Dia x 300mm FL, Uncoated, Plano-Convex Lens DWG NO 38643 SHEET SIZE A4 SHEET 1 OF 1	