





FOCAL LENGTH (EFL): 150 ±1,5

BACK FOCAL LENGTH (BFL): 147,33

- 1 532nm Laser AR Coating
R(ABS) < 0,25% @ 532nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 71,413 CX Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ - 5/ 10 - 5 6/ 10J-cm ⁻² ; 532nm; 20ns [20Hz]		GLASS Fused Silica 458/678	R ∞ PL Øe 11,7 (λ) SEE NOTE 1 3/ 2 (0,2) λ=632,8 nm 4/ 2,18' 5/ 10 - 5 6/ 10J-cm ⁻² ; 532nm; 20ns [20Hz]	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 355nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® 12,7mm Dia x 150mm FL, 532nm Laser AR Coating, 10J Coated, Plano-Convex Lens 38715	
		DWG NO	SHEET SIZE A4	SHEET 1 OF 1