





FOCAL LENGTH (EFL): 200 ± 2

BACK FOCAL LENGTH (BFL): 197,35

- 1 1064nm Laser AR Coating
R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 95,218 CX			GLASS Fused Silica 458/678	R ∞ PL		
Øe 11,7				Øe 11,7		
⌀ SEE NOTE 1				⌀ SEE NOTE 1		
3/ 2 (0,2) λ=632,8 nm				3/ 2 (0,2) λ=632,8 nm		
4/ -				4/ 2,18'		
5/ 10 - 5				5/ 10 - 5		
6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]			6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 355nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	12,7mm Dia x 200mm FL, 1064nm Laser AR Coating, 15J Coated, Plano-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	38739
			SHEET SIZE A4			SHEET 1 OF 1