



NOTES:


- 1. SUBSTRATE: FUSED SILICA
- 2. BEAM MODE: SM OR MM
- 3. OVERALL EFFICIENCY: 72%
- 4. FULL ANGLE(°): 2.75 x 2.75
- 5. COATING:
Laser V-Coat (1064nm)
- 6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 5mm
OUTPUT SHAPE: SQUARE:



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	1064nm, 20mm DIA., SQUARE OUTPUT, HIGH HOMOGENEITY DIFFRACTIVE DIFFUSER		
SHAPE	PLANO	PLANO						
MIN CLEAR APERTURE	Ø18.00	Ø18.00						
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	14681	SHEET 1 OF 1	