



NOTES:

1. SUBSTRATE: FUSED SILICA
2. BEAM MODE: SM OR MM
3. SAMPLED ENERGY: 82
4. SAMPLED ANGLE: 1.27
5. COATING:
LASER V-COAT (355nm)
6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 0.48mm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2						
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 		TITLE	355nm, 25.4mm Dia., 1x6 SPOT ARRAY, DIFFRACTIVE BEAMSPLITTER		
MIN CLEAR APERTURE	Ø22.9	Ø22.9	ALL DIMS IN	mm	DWG NO	14690	SHEET 1 OF 1	
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED						