



NOTES:

1. SUBSTRATE: ZINC SELENIDE (ZnSe)
2. BEAM MODE: SM OR MM
3. SAMPLED ENERGY: $1.22 \pm 0.15\%$
4. SAMPLED ANGLE: 21.06°
5. COATING:
LASER V-VCOAT ($10.6\mu\text{m}$)
6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 0.09mm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION		TITLE	10.6 μm , 25.4mm, DIFFRACTIVE BEAM SAMPLER	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	14696	SHEET 1 OF 1
MIN CLEAR APERTURE	$\varnothing 22.9$	$\varnothing 22.9$					
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					