





FOCAL LENGTH (EFL): 100 ±1
BACK FOCAL LENGTH (BFL): 97,32

- 1 1064nm Laser AR Coating
R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE			
R 47,609 CX			GLASS Fused Silica 458/678	R ∞ PL			
Øe 11,7				Øe 11,7			
⌀ SEE NOTE 1				⌀ SEE NOTE 1			
3/ 2 (0,2) λ=632,8 nm				3/ 2 (0,2) λ=632,8 nm			
4/ -				4/ 2,18'			
5/ 10 - 5				5/ 10 - 5			
6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]			6/ 15J-cm ⁻² ; 1064nm; 20ns [20Hz]				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 355nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 12,7mm Dia x 100mm FL, 1064nm Laser AR Coating, 15J Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING							
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 38737	SHEET SIZE A4	SHEET 1 OF 1