


PN: HH-226-I-Y-A



INPUT PARAMETER

Wavelength [nm]:	1064
Minimum Beam Diameter [mm]:	5
Beam Mode:	SM or MM

ELEMENT PARAMETER

Element Type:	Window
Material:	Fused Silica
Element Size [mm]:	20
Clear Aperture [mm]:	18
Thickness [mm]:	3
Coating:	AR/AR coating

OUTPUT PARAMETER

Output Shape:	Square
Full angle [deg]:	2.75x2.75
Transmission efficiency:	Close to 100%
Overall Efficiency:	~ 72%
Remarks	High Homogeneity

Holo/Or can improve the performances of this item. Please send us your requirements