





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	493
FULL WIDTH HALF MAX (FWHM)	160
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics<sup>®</sup>**

TITLE: SCHOTT BG-18 (VIS) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46052

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	526
FULL WIDTH HALF MAX (FWHM)	120
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics®**

TITLE: SCHOTT VG-9 (VIS) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46054

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	470
FULL WIDTH HALF MAX (FWHM)	271
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics®**

TITLE: SCHOTT BG-38 (VIS) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46434

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	330
FULL WIDTH HALF MAX (FWHM)	140
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics®**

TITLE: HOYA U-330 (UV) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46438

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	340
FULL WIDTH HALF MAX (FWHM)	85
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics®**

TITLE: HOYA U-340 (UV) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46440

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	830
FULL WIDTH HALF MAX (FWHM)	260
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics®**

TITLE: HOYA RT-830 (IR) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46444

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	356
FULL WIDTH HALF MAX (FWHM)	146
SURFACE QUALITY	80-50
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics®**

TITLE: SCHOTT BG-3 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 48638

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	390
FULL WIDTH HALF MAX (FWHM)	125
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: HOYA B-390 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 48640

SHEET 1 OF 1