






NOTES:


1. SUBSTRATE:  
HOYA GLASS: ND-70
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <0.02 mm
3.  FINE GRIND SURFACE
4. COATING SPECIFICATION:  
S1 & S2:R(AVG)  $\leq 0.4\%$  @ 425 - 675nm
5. OPTICAL DENSITY: 0.15 +/- 0.03 @400-700nm
6. TRANSMISSION (%): 70.0% AVERAGE FROM 400-700nm
7. ROHS COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	THIRD ANGLE PROJECTION 		TITLE	0.15 OD, 12.5mm DIA., VIS 0° COATED, ABSORPTIVE ND FILTER		
SHAPE	PLANO	PLANO			TITLE			
SURFACE QUALITY	80-50	80-50			TITLE			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	13079	SHEET 1 OF 1	