



NOTES:

1. SUBSTRATE:
ACRYLIC V825
nd=1.491
2. FOCAL LENGTH TOLERANCE:
3. DESIGN WAVELENGTH: 550nm
4. COATING

S1 & S2: NONE

5. ROHS: COMPLIANT



6. RADIUS IS NOT CONTINUOUS DUE TO GATE ON S3
USED DURING MANUFACTURING



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	CONVEX
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	7.00	7.00
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

EFL(mm): 6.90		 Edmund Optics®	
BFL(mm): 6.11			
THIRD ANGLE PROJECTION 		TITLE	8mm Dia. x 6.9mm FL, SMALL DIAMETER PLASTIC ASPHERE
ALL DIMS IN	mm	DWG NO	14572
			SHEET 1 OF 1