




1. SUBSTRATE MATERIAL:
FLOAT GLASS
2. COATING (APPLY ACROSS CLEAR APERTURE):
S1: ALUMINUM
S2: NONE
3. WAVELENGTH RANGE: 150 - 800nm
NOMINAL BLAZE WAVELENGTH: 150 - 800nm
GROOVE DENSITY: 2400 GROOVES/mm

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



			THIRD ANGLE PROJECTION 		TITLE 2400 GROOVES, 25x25mm, 150-800nm HOLOGRAPHIC HIGH PERFORMANCE REFLECTION GRATING	
	S1	S2				
SHAPE	PLANO	PLANO	ALL DIMS IN mm		DWG NO 15758	
CLEAR APERTURE	22.5 x 22.5	22.5 x 22.5				
					SHEET 1 OF 1	