




NOTES:

1. SUBSTRATE MATERIAL:
FLOAT GLASS
2. COATING (APPLW ACROSS CLEAR APERTURE):
S1: GOLD
S2: NONE
3. WAVELENGTH RANGE: nm
NOMINAL BLAZE WAVELENGTH: 500nm
GROOVE DENSITY:600 GROOVES/mm
4. EDGES GROUND
5. RoHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® **Edmund Optics**®

600 GROOVES, 30x30mm, RULED GOLD HIGH
PERFORMANCE REFLECTION GRATING

	S1	S2	THIRD ANGLE PROJECTION		TITLE	600 GROOVES, 30x30mm, RULED GOLD HIGH PERFORMANCE REFLECTION GRATING	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	15777	SHEET 1 OF 1
CLEAR APERTURE	27.0 x 27.0	27.0 x 27.0					