




NOTES:

- 1. SUBSTRATE: D263
- 2. DIFFRACTION: 10° @ 915nm
- 3. COATING (APPLY ACROSS COATING APERTURE)  
S1 & S2:  
R(ABS) < 0.5% @ 915nm
- 4. GROOVE DENSITY: 190 grooves/mm



**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø24.5	Ø24.5
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

TITLE	915nm Laser V-Coat, 25mm Square, 10° Diffraction Polarization Grating		
DWG NO	16592		SHEET 1 OF 1