



NOTES:

1. SUBSTRATE:
D-ZK3
2. NUMERICAL APERTURE: 0.54
3. COATING
S1 & S2: R(AVG) $\leq 0.5\%$ @ 350 - 700nm
4. FOCAL LENGTH TOLERANCE: $\pm 1\%$
5. TRANSMITTED WAVEFRONT ERROR (λ , RMS @ 632.8NM): < 0.087
6. DESIGN WAVELENGTH: 633nm



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	6.75	Edmund Optics®	TITLE LightPath 354115 9.2mm Dia., 0.54 NA, BBAR (350-700nm), Molded Aspheric Lens
SHAPE	CONVEX	PLANO	WD	4.30		
SURFACE QUALITY	60-40	60-40	THIRD ANGLE PROJECTION		DWG NO	16691
CLEAR APERTURE	$\phi 7.00$	$\phi 5.30$	ALL DIMS IN	mm		SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				