

NOTES:


1. SUBSTRATE:
FUSED SILICA
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Ultrafast-Enhanced Silver
R(AVG) >99% @ 850-1150nm @ 0° AOI
Rs >99% @ 800-1150nm @ 45° AOI
Rp >98.5% @ 850-1100nm @ 45° AOI
GDD: 0 ±30 fs² @ 800 - 1150 nm

S2: NONE


3. FINE GRIND SURFACE

4. EFL (EFFECTIVE FOCAL LENGTH): 50mm
5. Damage Threshold, Pulsed:
0.4 J/cm² @ 1030nm, 200fs, 1 pulse (typical)
0.18 J/cm² @ 1030nm, 200fs, 100Hz, 1000 pulses (typical)



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	Edmund Optics® 800-1150nm, 50.8mm Dia. x 50mm EFL, Ultrafast-Enhanced Silver Concave Mirror			
SHAPE	CONCAVE	PLANO				
RADIUS	100.00	INFINITY	THIRD ANGLE PROJECTION 			
SURFACE QUALITY	20-10	N/A				
CLEAR APERTURE	45.72mm	N/A	ALL DIMS IN mm			
IRREGULARITY AT 632.8nm	0.15λ	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	DWG NO		17273	SHEET 1 OF 1