






**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	330
FULL WIDTH HALF MAX (FWHM)	140
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm





 **Edmund Optics®**

TITLE: HOYA U-330 (UV) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46438

SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	340
FULL WIDTH HALF MAX (FWHM)	85
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: HOYA U-340 (UV) 50.8mm Square, Colored Glass Bandpass Filter




DWG NO: 46440

SHEET 1 OF 1

NOTES:

1. SUBSTRATE: BG3
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY





	S1
SHAPE	PLANO
TRANSMISSION RANGE	DEEP BLUE
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED



**EO**® Edmund Optics®

TITLE	SCHOTT BG3 50 x 50mm COLORED BANDPASS FILTER, 3mm THK		
DWG NO	14405	SHEET	1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	390
FULL WIDTH HALF MAX (FWHM)	125
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: HOYA B-390 (UV-VIS) 50.8mm Square, Colored Glass Bandpass Filter




DWG NO: 48640

SHEET 1 OF 1

NOTES:

1. SUBSTRATE: BG38
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
TRANSMISSION RANGE	BLUE - GREEN
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

SCHOTT BG38 50 x 50mm COLORED  
BANDPASS FILTER, 3mm THK

DWG NO




14417

SHEET  
1 OF 1

NOTES:

1. SUBSTRATE: BG18
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1
SHAPE	PLANO
TRANSMISSION RANGE	BLUE - GREEN
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

SCHOTT BG18 50 x 50mm COLORED  
BANDPASS FILTER, 3mm THK

DWG NO




14411

SHEET  
1 OF 1

NOTES:

1. SUBSTRATE: VG9
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN 1 ARCMIN

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY





	S1
SHAPE	PLANO
TRANSMISSION RANGE	VIOLET - GREEN
SURFACE QUALITY	60-40
CLEAR APERTURE	48.50 x 48.50
BEVEL MAX FACE	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION	
ALL DIMS IN	mm

**EO**® **Edmund Optics**®

TITLE	SCHOTT VG9 50 x 50mm COLORED BANDPASS FILTER, 3mm THK
DWG NO	14444
	SHEET 1 OF 1


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
CENTER WAVELENGTH	830
FULL WIDTH HALF MAX (FWHM)	260
SURFACE QUALITY	60-40
COATING TYPE	Uncoated
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE: HOYA RT-830 (IR) 50.8mm Square, Colored Glass Bandpass Filter

DWG NO: 46444

SHEET 1 OF 1