

NOTES:

1. SUBSTRATE:  
Fused Silica
2. CENTERING TOLERANCE (AT 587.6nm): <1ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)  
S1: NONE  
S2: NONE

4. EDGES: FINE GROUND


5. ASPHERIC FIGURE ERROR: 0.250 µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$


**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**


SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



COEFFIECIENT TABLE 6.	
COEFFIECIENT	S1
SEMI-DIAMETER	2.500000E+01
(1/RADIUS)	4.200798E-02
k	-7.730000E-01
D	0.000000E+00
E	2.068684E-06
F	9.798870E-10
G	3.683270E-13
H	1.905505E-16
J	0.000000E+00
L	0.000000E+00

	S1	S2
SHAPE	CONVEX	CONVEX
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø 45.00mm	Ø 45.00mm
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL @ 355nm:50.00	
BFL @ 355nm: 37.00	
THIRD ANGLE PROJECTION	
	
ALL DIMS IN	mm

 **Edmund Optics®**

TITLE	50mm Dia 0.48 NA Uncoated, UV Fused Silica Aspheric Lens
DWG NO	17334
SHEET	1 OF 1