

NOTES:

1. SUBSTRATE MATERIAL:
NITROCELLULOSE

2. COATING (APPLY ACROSS COATING APERTURE)



S1: NONE

45% R @ 3000 - 5000nm @ 45° AOI


55% T @ 3000 - 5000nm @ 45° AOI

S2: NONE

3. ROHS : COMPLIANT



SECTION A-A



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø101.60	Ø101.60
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

EO® **Edmund Optics**®

TITLE

101.6mm Clear Aperture 45R/55T, Infrared
Pellicle Beamsplitter

DWG NO

19284

SHEET
1 OF 1