NOTES:

- 1. SUBSTRATE: SAPPHIRE (AL2O3)
- 2. SURFACE \$1 TO BE PARALLEL WITH SURFACE \$2 TO WITHIN ≤3.5 ARCMIN
- 3. ENVIRONMENTAL REQUIREMENTS:

S1 & S2: HIGH DURABILITY BBAR (400-1100nm) ADHESION: PER MIL-M-13508C PARA 4.4.6 ABRASION: SEVERE PER MIL-C-675C PARA 4.5.10

HUMIDITY: PER MIL-C-675C PARA 4.5.8 SALT SOLUBILITY: PER MIL-C-675C PARA 4.5.7 SALT SPRAY: PER MIL-C-675C PARA 4.5.9

TEMPERATURE CYCLE: PER MIL-M-13508C PARA 4.4.4

4. REFLECTION PERFORMANCE ACROSS CLEAR APERTURE ON CENTER


S1 & S2:


R(AVG) <1.5% @ 400 - 1100nm R(ABS) <2.0% @ 400 - 1100nm



FINE GRIND SURFACE

6. ROHS COMPLIANT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	80-50	80-50		
CLEAR APERTURE	Ø 45.72	Ø 45.72		
SURFACE FLATNESS	2λ (typical)	2λ (typical)		
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED		

			Edmund Optic	S®
THIRD ANGLE PROJECTION		TITLE	50.8mm Dia., 3.18mm Thick, 400-1100nm, High Durability AR Coated Sapphire Window	
ALL DIMS IN	mm	DWG NO	18467	SHEET 1 OF 1

