




NOTES:


1. SUBSTRATE: POLYMER FILM XP42-70
2. OPERATING TEMPERATURE (°C): -10 to +60
3. OPERATING HUMIDITY (%): ≤80% (No Condensation)
3. WAVELENGTH RANGE: 400-700nm
4. POLARIZATION: >99.98
5. TRANSMISSION (%):  
SINGLE 42 ±2  
PARALLEL: 36.4  
CROSSED: <0.004
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	12.5mm Dia. Linear Polarizer (XP42-70)	
ALL DIMS IN	mm	DWG NO	19940	SHEET 1 OF 1