

NOTES:


- SUBSTRATE:
N-SF6
- CENTERING TOLERANCE (AT 587.6nm): <2.5 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE)
S1 & S2: V-COAT
R(abs) < 0.25% @ 1550nm @ 0° AOI

4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.25 µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



COEFFICIENT TABLE 6.	
COEFFICIENT	S1
SEMI-DIAMETER	1.250000E-01
(1/RADIUS)	2.622263E-02
k	-1.000000E-00
D	0.000000E+00
E	7.258095E-07
F	-5.885602E-11
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø 22.5mm	Ø 22.5mm
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL@1550nm: 50.00
BFL@587.6nm: 42.65
THIRD ANGLE PROJECTION
ALL DIMS IN mm



Edmund Optics®

25mm Dia., 0.25 NA, V-Coated 1550nm
NIR Aspheric Lens

TITLE	DWG NO	22940	SHEET 1 OF 1
-------	--------	-------	-----------------

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY