


NOTES:

1. SUBSTRATE: N-BK7
2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: VIS-NIR (400-1000nm)



S2: VIS-NIR (400-1000nm)

Rabs $\leq 0.25\%$ @ 880nm Ravg $\leq 1.25\%$ @ 400 - 870 nm Ravg $\leq 1.25\%$ @ 890 - 1000nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT

6. TRANSMITTED WAVEFRONT (P-V):
 $\lambda/4$ (per inch over clear aperture)



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	$\phi 27.00$	$\phi 27.00$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE
PROJECTION



Edmund Optics®

30mm Dia., 2mm Thick, VIS-NIR Coated
 $\lambda/4$ N-BK7 Window

ALL DIMS IN

mm

TITLE

DWG NO

23409

SHEET
39 OF 84