




NOTES:

1. SUBSTRATE:
Zinc Selenide (ZnSe)
2. PARALLELISM:
SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO <3 ARCMIN
3. COATING:
S1 & S2: R(AVG) <0.5% @ 8 - 12µm
R(ABS) <1% @ 8 - 12µm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	λ/20 @ 10.6µm	λ/20 @ 10.6µm
CLEAR APERTURE	Ø43.18	Ø43.18
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN mm

EO® Edmund Optics®

50.8mm Dia., 5mm Thick, 8-12µm BBAR Coated, ISP Optics Zinc Selenide (ZnSe) Window

TITLE

DWG NO

24682

SHEET 159 OF 175