


NOTES:

- 1. CRYSTAL TYPE: BBO
- 2. SURFACE S2 TO BE PARALLEL TO SURFACES S1 TO WITHIN <20 ARCSEC
- 3. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1: 515 & 1030nm AR Coating
  - S2: 515 & 1030nm AR Coating
- 4. ORIENTATION  $\Theta/\phi$  (°): 23.4/90
- 5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	$\lambda/4$	$\lambda/4$
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	>5	>5
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®	
ALL DIMS IN		TITLE	6 x 6 x 0.2, 1030nm SHG, Type I BBO Nonlinear Crystal
mm		DWG NO	24196
			SHEET 1 OF 1