


NOTES:


- 1. SUBSTRATE : Germanium (Ge)
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: UNCOATED
S2: UNCOATED

3. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 | | | | |
|-----------------------|----------------------|----------------------|--|----|--------|--|
| CLEAR APERTURE | 85% | 85% | | | | |
| ANGLE TOL. (arcmin) | ±10 | ±10 | | | | |
| SURFACE QUALITY | 60-40 | 60-40 | | | | |
| SURFACE FLATNESS | 2λ | 2λ | | | | |
| WAVELENGTH RANGE (nm) | 2000 - 14000 | 2000 - 14000 | | | | |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | | | | |
| | | | THIRD ANGLE PROJECTION  | | TITLE | Germanium, 25.4mm, Uncoated, ISP Optics IR Right Angle Prism |
| | | | ALL DIMS IN | mm | DWG NO | 25041 |
| | | | | | | SHEET 1 OF 1 |

 **Edmund Optics®**