


- NOTES:
- 1. SUBSTRATE: Fused Silica (Corning 7980)
  - 2. RoHS COMPLIANT
  - 3. SURFACE S2 TO BE PARALLEL WITH SURFACE S 1 TO WITHIN ACRMINS
  - 4. Coating (Apply Across Clear Aperture):  
S1 & S2: Ravg ≤0.5% @ 350 - 700nm

5. FINE GROUND SURFACE




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
Shape	Plano	Plano
Surface Accuracy	1λ	1λ
Surface Quality	60-40	60-40
Clear Aperture	45.72	45.72
Bevel	Protected as Needed	Protected as Needed

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

50.8mm Dia. 2mm Thick VIS-EXT Coated, 1λ  
Fused Silica Window

DWG NO

25334

SHEET  
91 OF 101