





FOCAL LENGTH (EFL): 50 ±0,5
BACK FOCAL LENGTH (BFL): 46,17

1 633nm V-COAT
R(ABS) < 0,25% @ 633nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 33,63 CX			GLASS N-SF5 673/322 Nd: 1,673 Vd: 32,25	R ∞ PL		
Øe 29				Øe 29		
⌂ SEE NOTE 1				⌂ SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 1,49'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 30mm Dia x 50mm FL, 633nm V-Coat Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26143
			SHEET T SIZE A4			SHEET 1 OF 1