





FOCAL LENGTH (EFL): 40 ±0,4
BACK FOCAL LENGTH (BFL): 37,2

- 1 532nm V-COAT
R(ABS) < 0,25% @ 532nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE				
R 31,39 CX			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL				
Øe 29				Øe 29				
⌀ SEE NOTE 1				⌀ SEE NOTE 1				
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm				
4/ -				4/ 1,27'				
5/ 40 - 20				5/ 40 - 20				
6/ -			6/ -					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	30mm Dia x 40mm FL, 532nm V-Coat Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26133	SHEET T SIZE A4	SHEET 1 OF 1