





FOCAL LENGTH (EFL): 120 ±1,2
BACK FOCAL LENGTH (BFL): 116,04

1 633nm V-COAT
R(ABS) < 0,25% @ 633nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 62,02 CX			GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL		
Øe 29				Øe 29		
SEE NOTE 1				SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 1,93'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	30mm Dia x 120mm FL, 633nm V-Coat Coated, Plano-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26145
					SHEET T SIZE A4	SHEET 1 OF 1