






FOCAL LENGTH (EFL): 100 ± 1

BACK FOCAL LENGTH (BFL): 96,01

- 1 532nm V-COAT
R(ABS) < 0,25% @ 532nm @ 0° AOI

LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R 51,68 CX			GLASS N-BK7 517/642		R ∞ PL			
Øe 29			Nd: 1,517		Øe 29			
SEE NOTE 1			Vd: 64,17		SEE NOTE 1			
3/ 3 (0,5) λ=632,8 nm					3/ 3 (0,5) λ=632,8 nm			
4/ -					4/ 1,93'			
5/ 40 - 20					5/ 40 - 20			
6/ -					6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 30mm Dia x 100mm FL, 532nm V-Coat Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26135	SHEET SIZE A4	SHEET 1 OF 1