




FOCAL LENGTH (EFL): 40 ±0,4
BACK FOCAL LENGTH (BFL): 35,13

- 1 785nm V-COAT
R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE			
R 31,389 CX		GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL			
Øe 39			Øe 39			
⌀ SEE NOTE 1			⌀ SEE NOTE 1			
3/ 3 (0,5) λ=632,8 nm			3/ 3 (0,5) λ=632,8 nm			
4/ -			4/ 1,27'			
5/ 40 - 20			5/ 40 - 20			
6/ -		6/ -				
PROTECTIVE CHAMFERS AS NEEDED			Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE 40mm Dia x 40mm FL, 785nm V-Coat Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO	26155	SHEET T SIZE A4	SHEET 1 OF 1