





FOCAL LENGTH (EFL): 40 ±0,4

BACK FOCAL LENGTH (BFL): 35,13

- 1 1550nm V-COAT
R(ABS) < 0,25% @ 1550nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 31,389 CX			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL		
Øe 39				Øe 39		
SEE NOTE 1				SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 1,27'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 40mm Dia x 40mm FL, 1550nm V-Coat Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 26174	
					SHEET T SIZE A4	SHEET 1 OF 1