





- NOTES:
- 1. SUBSTRATE: SODIUM SILICATE GLASS DOPED WITH SILVER NANOPARTICLES
 - 2. COATING: Single-Side AR
 - 3. TYPICAL ENERGY DENSITY LIMIT: 10 W/cm2
 - 4. EXTINCTION RATIO: >10,000:1
 - 5. WAVELENGTH RANGE: 1260-1360
 - 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	40 - 20	40 - 20				
TRANSMISSION (%)	>91	>91	THIRD ANGLE PROJECTION		TITLE	Ultra-Thin Polarizer, 1310nm, 25mm Dia, Single AR
ACCEPTANCE ANGLE	±20°	±20°			DWG NO	26640
BEVEL MAX FACE	PROTECTED AS NEEDED	PROTECTED AS NEEDED				
			ALL DIMS IN	mm		SHEET 2 OF 12