




FOCAL LENGTH (EFL): 75 ±0,75
BACK FOCAL LENGTH (BFL): 53,49

- 1 YAG-BBAR
R(ABS) < 0,25% @ 532nm @ 0° AOI
R(ABS) < 0,25% @ 1064nm @ 0° AOI
R(AVG) < 1,0% FROM 500 - 1100nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 38,76 CX Øe 73,5 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 73,5 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE	75mm Dia x 75mm FL, YAG-BBAR Coated, Plano-Convex Lens	
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm		DWG NO	26114	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				SHEET 1 OF 1			
INDICATIONS IN ACCORDANCE WITH ISO 10110							