




- NOTES:
- 1. SUBSTRATE: SODIUM SILICATE GLASS DOPED WITH SILVER NANOPARTICLES
 - 2. COATING: Double-Side AR
 - 3. TYPICAL ENERGY DENSITY LIMIT: 10 W/cm2
 - 4. EXTINCTION RATIO: >10,000:1
 - 5. WAVELENGTH RANGE: 1260-1360
 - 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2			 Edmund Optics®			
SHAPE	PLANO	PLANO			TITLE	Ultra-Thin Polarizer, 1310nm, 25mm Dia, AR		
SURFACE QUALITY	40 - 20	40 - 20				DWG NO	26646	
TRANSMISSION (%)	>95	>95						
ACCEPTANCE ANGLE	±20°	±20°						
BEVEL MAX FACE	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	26646	SHEET 6 OF 12	