




FOCAL LENGTH (EFL): $24 \pm 0,24$
 BACK FOCAL LENGTH (BFL): $22,63$

- 1 NIR I
 $R(\text{AVG}) \leq 0,5\%$ FROM 600 - 1050nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 11,003 CX Øe 5,4 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 5,4 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION 	Edmund Optics® TITLE 6mm Dia x 24mm FL, NIR I Coated, Plano-Convex Lens DWG NO 26330	
ALL DIMS IN: mm			SHEET SIZE A4 SHEET 1 OF 1	