





FOCAL LENGTH (EFL): $36 \pm 0,36$
 BACK FOCAL LENGTH (BFL): $34,63$

- 1 1550nm V-COAT
 R(ABS) < 0,25% @ 1550nm @ 0° AOI

LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R 16,505 CX			GLASS Fused Silica 458/678 Nd: 1,458		R ∞ PL		
Øe 5,4					Øe 5,4		
SEE NOTE 1					SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm					3/ 3 (0,5) λ=632,8 nm		
4/ -					4/ 2,18'		
5/ 40 - 20					5/ 40 - 20		
6/ -			6/ -				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®		
ROHS: COMPLIANT SCALE: NONE λ = 587,6nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 6mm Dia x 36mm FL, 1550NM V-COAT Coated, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING							
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm		DWG NO 25890		
					SHEET T SIZE A4		
					SHEET 1 OF 1		