





FOCAL LENGTH (EFL): 100 ±1

BACK FOCAL LENGTH (BFL): 97,13

- 1 VIS-NIR
R(ABS) ≤ 0,25% @ 880nm @ 0° AOI
R(AVG) ≤ 1,25% FROM 400 - 870nm @ 0° AOI
R(AVG) ≤ 1,25% FROM 890 - 1000nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 90,38 CX			GLASS Fused Silica 458/678 Nd: 1,458	R 90,38 CX		
Øe 49				Øe 49		
⌂ SEE NOTE 1				⌂ SEE NOTE 1		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ -				4/ 2,18'		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 50mm Dia x 100mm FL, VIS-NIR Coated, Double-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26621
					SHEET T SIZE	A4
					SHEET	1 OF 1