





FOCAL LENGTH (EFL): 12 ±0,12
BACK FOCAL LENGTH (BFL): 10,63

1 1064nm V-COAT
R(ABS) < 0,25% @ 1064nm @ 0° AOI

LEFT SURFACE			MATERIAL		RIGHT SURFACE			
R 5,5 CX			GLASS Fused Silica 458/678 Nd: 1,458		R ∞ PL			
Øe 5,4					Øe 5,4			
λ SEE NOTE 1					λ SEE NOTE 1			
3/ 3 (0,5) λ=632,8 nm					3/ 3 (0,5) λ=632,8 nm			
4/ -					4/ 2,18'			
5/ 40 - 20					5/ 40 - 20			
6/ -			6/ -					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 6mm Dia x 12mm FL, 1064NM V- COAT Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	25879	SHEET T SIZE A4	SHEET 1 OF 1