





FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): 15,94

- 1 1550nm V-COAT
 R(ABS) < 0,25% @ 1550nm @ 0° AOI

LEFT SURFACE			MATERIAL	RIGHT SURFACE			
R 8,25 CX			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL			
Øe 8,1				Øe 8,1			
SEE NOTE 1				SEE NOTE 1			
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm			
4/ -				4/ 2,18'			
5/ 40 - 20				5/ 40 - 20			
6/ -			6/ -				
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 9mm Dia x 18mm FL, 1550NM V- COAT Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING							
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 25892	SHEET T SIZE A4	SHEET 1 OF 1