




FOCAL LENGTH (EFL): $-48 \pm 0,48$

BACK FOCAL LENGTH (BFL): $-50,31$

- 1 VIS-EXT
 $R(\text{AVG}) \leq 0,5\%$ FROM 350 - 700nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 24,81 CV Øe 11 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 11 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	12mm Dia x -48mm FL, VIS-EXT Coated, Plano-Concave Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	26660	SHEET T SIZE	A4	SHEET 1 OF 1