

NOTES:

1. SUBSTRATE: Fused Silica

2. COATING (APPLY ACROSS CLEAR APERTURE)



S1&S2: Ravg ≤0.4% @ 425 - 675nm

3.  ARROW POINTS TOWARD TILTED SURFACE

4.  FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE


6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
RADIUS	INFINITY	INFINITY
MINI CLEAR APERTURE	$\phi 22.50$	$\phi 22.50$
SURFACE QUALITY	20-10	20-10
SURFACE ACCURACY	$\lambda/10$	$\lambda/10$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

25mm Dia., VIS 0° Coated, 30' Wedge, Fused Silica Wedged Window

DWG NO

25616

SHEET
2 OF 15