


NOTES:

1. SUBSTRATE: XP42-300 ON PMMA
2. WAVELENGTH RANGE (nm): 400 - 700
3. EXTINCTION RATIO: 9000:1
4. OPERATING TEMPERATURE (°C): -40 to +80
5. TRANSMISSION (%):  
SINGLE: 42  
PARALLEL: 36  
CROSSED: <0.004
6. RoHS: COMPLIANT

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® Edmund Optics®

THE POLARIZERS CONSISTS OF A POLYMER POLARIZATION  
FILM LAMINATED ONTO PMMA.

THIRD ANGLE PROJECTION		TITLE		600 x 450mm Linear Plastic Polarizer (XP42-300)	
ALL DIMS IN	mm	DWG NO	24283	SHEET 1 OF 1	