




NOTES:

- 1. SUBSTRATE: Fused Silica
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1&S2: Rabs ≤1.5% @ 750 - 800nm
 - Ravg ≤0.7% @ 750 - 1550nm
 - Rabs ≤1.0% @ 800 - 1550nm
- 3.  ARROW POINTS TOWARD TILTED SURFACE
- 4.  FINE GRIND SURFACE
- 5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 6. ROHS COMPLIANT



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
RADIUS	INFINITY	INFINITY
MINI CLEAR APERTURE	Ø 11.25	Ø 11.25
SURFACE QUALITY	20-10	20-10
SURFACE ACCURACY	λ/10	λ/10
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	12.5mm Dia., NIR II Coated, 30' Wedge, Fused Silica Wedged Window
ALL DIMS IN	mm	DWG NO	25621
			SHEET 7 OF 15