




FOCAL LENGTH (EFL): -100 ± 1

BACK FOCAL LENGTH (BFL): $-102,31$

- 1 VIS-EXT
 $R(\text{AVG}) \leq 0,5\%$ FROM 350 - 700nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 51,68 CV $\varnothing_e$ 24 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ - 5/ 40 - 20 6/ -	GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL $\varnothing_e$ 24 λ SEE NOTE 1 3/ 3 (0,5) $\lambda=632,8$ nm 4/ 1,93' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®					
ROHS: COMPLIANT	SCALE: NONE	$\lambda = 587,6\text{nm}$			TITLE	25mm Dia x -100mm FL, VIS-EXT Coated, Plano-Concave Lens			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY									
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	mm	DWG NO	26665		SHEET T SIZE	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110						A4			